

Electronic dial gauge

MarCator 1086 Ri



Application:

For static measurements of lengths and length differences

Version:

- Factor adjustable
- Large and high-contrast LCD display
- Digit height 11 mm
- With Integrated Wireless
- Permissible deviation MPEp for increment 0.0005=2 µm, for increment 0.01=20 µm
- mm/inch changeover

Advantage:

- LOCK function (key lock)

Delivery:

In case with CR 2450 battery



Art. no.	33166 860
Length measuring range	100 mm
Digit increment	0.0005 mm
Min./max. measurement force	1.6-3.5 N
Error limit	8 µm
Repeat accuracy	2 µm
Data transmission type	multiCOM/MarConnect
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Tolerance value entry	Yes
Calibration Group	CE
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
WEEE (taking back waste electrical and electronic equipment)	5

EAN-Code

4059 1920 14568