

LED workplace light Floodlight

With and without dimmer



Execution:

- LED light, with flexible light arm, rubber-coated
- Low power consumption and low heat generation
- Solid and robust design for heavy-duty use
- High-performance chip with lamp life of min. 50,000 operating hours
- Anti-glare and flicker-free light, low reflection, with 24 V power supply
- Luminous flux: 1200 lumen, colour temperature: daylight white, approx. 5500 Kelvin, 160 degree uniform illumination
- 88-mm magnetic base with 420 N adhesive force
- Total length 850 mm, light head 175 x 50 x 25 mm
- Ref. no. 160: No dimmer
- Ref. no. 162: With dimmer (continuously variable)

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



| | |
|---------------------------------|------------------|
| Art. no. | 56879 162 |
| Brand | BAUER & BÖCKER |
| Manufacturer Part Number | 900/43D |
| Power rating | 10 W |
| Arm length | 701 mm |
| IP protection class | IP 65 |
| Dimmable | Yes |
| Gross Weight | 1.500 kg |
| Product Group | 5ID |

EAN

4260131238079