

## Pneumatic hand belt sander HBH 200

300 watt



### Application:


For finer and flat grinding applications.

### Version:

- Air discharge to the rear
- For holding interchangeable sanding arms.

### Delivery:

Without hose unit, without grinding arm



<b>Art. no.</b>	<b>75068 017</b>
<b>Model</b>	HBH 200
<b>Max. idle speed</b>	20000 rpm
<b>Power input</b>	300 W
<b>Air consumption</b>	500 l/min
<b>Diameter of housing</b>	41 mm
<b>Connection thread</b>	G 1/8 inch
<b>Length</b>	247 mm
<b>Inner hose diameter</b>	7 mm
<b>Min. sanding belt width</b>	8 mm
<b>Max. sanding belt width</b>	20 mm
<b>Weight</b>	0.87 kg