



NOTES:

1. MATERIALS:
 HOOD: PBT GF UL94 V-0 BLACK
 FRONTSEALING: SILICONE VMQ BLUE
 SCREW: STAINLESS STEEL
 O-RING: NBR BLACK
2. TEMPERATURE RANGE: -30°C TO +90°C
3. RECOMMENDED TORQUE FOR SCREW:
 35Ncm (3.1 in.LB)
 MAX. TORQUE: 68Ncm (6 in.LB)
4. SINGLE PACKED

* COMPLETELY TIGHTENED

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance		dim. in mm		scale:		1,5:1 (1:1)
	±0,3 unless otherw. specified				material:		SEE NOTES
	date	name		title:		WATER RESISTANT D-SUB HOOD 50 POS. JACKSREW 4-40 UNC STAINLESS STEEL	
	drawn 06.02.2014	Heinrich		dwg no:			
appd. 06.02.2014	Huether		norm		sh: 1		
rev.	description	date	name			part no: 15-004700	