







## DIL sockets

Order code	Manufacturer code	Description
22-0100	n/a	3 PIN TO18 TRANS + IC HOLDER (RC)
22-0105	n/a	3 PIN TO5 TRANS AND IC HOLDER (RC)

DIL sockets	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

## TRANSISTOR SOCKETS



CONTACT RESISTANCE:	10m $\Omega$	
CURRENT RATING MAX:	1.0amp	
CAPACITANCE		
CONTACT TO CONTACT:	0.70pf	
INSERTION FORCE:	200G	3 Pin
(TYPICAL)		0.2" PCD
WITHDRAWAL FORCE:	150G	
(TYPICAL)		
MAX ACCEPTABLE		
PIN SIZE:	0.020"	
TEMP RANGE:	-65°C to -150°C	
MATERIAL PLASTIC:	PBT 30% Glass	
MATERIAL CONTACT:	Ph Br	