


FE-30-A-A-R6/2M

Fibre optics



Product characteristics

Through-beam sensor

Ø 6 mm

Sensing range 240 mm

Connection to fibre optic amplifiers type OIF

Range

Sensing range	OIF: 240 mm
---------------	-------------

Environment

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Design	angled
--------	--------

Length [mm]	2000
-------------	------

Min. bending radius [mm]	30, for fixed installation
--------------------------	----------------------------

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

aluminium; adapter: polyamide

Weight [kg]

0.217

Accessories

Accessories (included)

E10221

Remarks

Pack quantity [piece]

1