



SLIMLINE LIGHT WITH MOTION DETECTOR SL 025  
W/O POW. OUL. WITH MAGN.(CA.30N)

Figure similar

Model		
product brand name		SIVACON
Type of light source		compact fluorescent light
General technical data		
Active power consumption / of the light source	W	11
Protection class		
Protection class IP		IP20
Product details		
Product component		
• ON/OFF switch		No
• Light sensor		Yes
• socket outlet		Yes
Product property / magnetic		Yes
Mechanical Design		
Height	mm	91
Width	mm	345
Depth	mm	40
Length	mm	345
Material		plastic
Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MF59102B>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8MF59102B/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MF59102B](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MF59102B)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015