


**Actuator/sensor cable, PVC
extension cable
RKS4.4T-0,6-RSS4.4T/TEL**



- Female M12, straight, 4-pin
- Shield on coupling nut/screw
- Male M12, straight, 4-pin
- Sheath material: PVC, shielded
- Sheath color: black
- Resistant to chemicals and oils
- Flame retardant
- Resistant to acids and alkaline solutions
- Resistant to microbes and hydrolysis
- LABS free
- Approval: cULus
- RoHS conform
- Protection class IP67
- Cable length: 0.6 m

Type designation RKS4.4T-0,6-RSS4.4T/TEL
Ident no. 6626346


Connector A side
Number of pins Female connector, M12 ♂ 1, Straight
4
Contacts Brass, CuZn, Gold-plated
Contact carriers Plastic, TPU, Black
Grip Plastic, TPU, Black
Coupling nut/screw Brass, CuZn, Nickel-plated
Seal Plastic, FPM/FKM
Protection class IP67, A + B side screwed together
Mechanical lifespan > 100 Mating cycles
Pollution degree 3
Tightening torque 0.8 ... 1 Nm
(observe max. torque of counter piece!)

Connector B side
Number of pins Connector, M12 x 1, Straight
4 pins
Contacts brass, CuZn, Gold-plated
Contact carriers Plastic, TPU, Black
Grip plastic, TPU, black
Coupling nut/screw Brass, CuZn, Nickel-plated
Protection class IP67, only in screwed state
Mechanical lifespan > 100 Mating cycles
Pollution degree 3
Tightening torque 0.8 ... 1 Nm
(observe max. torque of counter piece!)

General data
Cable diameter 5.4 ± 0.20mm
Cable length 0.6 m
Cable quality PVC
Cable color Black
Core insulation PVC
Core colors BN, WH, BU, BK
Core cross-section 4x0.34mm²
Arrangement of strands 42x0.1 mm
Shielding Aluminum foil, tinned copper wire


Electrical features at +20 °C
Current 4 A
Rated voltage 250 V
Insulation resistance > 30.5 MΩ/km
Test voltage 2000 V
Forward resistance max. 57 Ω/km

Cable Cross-section



Drawing shows design status including hexagon coupling nut
(Start of production CW42/2016).

Circuit Diagram



**Actuator/sensor cable, PVC
extension cable
RKS4.4T-0,6-RSS4.4T/TEL****Mechanical and chemical properties**

Bending radius (stationary laying)	> 5 x Ø
Bending radius (flexible use)	> 10 x Ø
Ambient temperature	
Stationary	-40...+105°C
In motion	0...+80°C

**Actuator/sensor cable, PVC
extension cable
RKS4.4T-0,6-RSS4.4T/TEL**

TURCK

Industrial
Automation

Accessories

Type code	Ident no.	Description	
Torque-Wrench-Set-AS	6936170	Torque wrench set; handles with adjustable torque 0.4-1.0 Nm, torque wrench for M8 (SW9), fork wrench for M12 (SW 14)	
BLANK-LABEL-FOR-CORDESETS-TEL-TXL	6936206	Label for TEL and TXL cables, length: 18 mm, height: 4 mm, material: polycarbonate (PC), color: white, halogen-free and flame-retardant	