

Hot air tool - Professional Line

# HG 2320 E

Folding box  
EAN 4007841 007386  
Article number 007386



CE



VDE

## Function description

Precision digital control. Electronically controlled HG 2320 E hot air tool. 2300 W, digital temperature setting by joystick from 80 – 650 °C, temperature indicated in 10 °C steps on LCD display. Infinitely variable air volume regulation from 150 - 500 l/min and 4 memory programmes to save desired settings.

## Technical specifications

Temperature	80 – 650 °C	Function, life expectancy, heating element	600 h
Airflow rate	150 – 500 l/min	Replaceable heating element	No
Temperature setting	in 10°C steps by joystick	Restart protection	No
Settings made via	joystick	Temperature scanner	Yes
Temperature display	LCD display	Fine dust filter	No
Airflow control	Settings	Thermal cut-out	Yes
Programming function	Yes	Thermostat	Yes
Loc function	Yes	ESD	No
Residual heat indicator	Yes	Nozzle receiver, type	34
Cool function	No	Cord length	3 m
Motor, type	Brush motor	Dimensions (L x W x H)	253 x 87 x 200 mm
Heating element	Ceramic heating element	PU1, net weight	1,024 kg
Mains power supply	220 – 230 V / 50 – 60 Hz	Manufacturer's Warranty	1 year
Function, hanger	Yes	PU1, EAN	4007841007386
Function, life expectancy, motor	1000 h		

# HG 2320 E

Folding box  
 EAN 4007841 007386  
 Article number 007386



## Accessories

EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 034566	HL Tool Stand
EAN 4007841 010294	Sieve reflector nozzle 50 x 35 mmT421T399:T827
EAN 4007841 009571	Reduction nozzle 6 mm
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 070618	Reduction nozzle 9 mm
EAN 4007841 073114	PVC plastic welding rod
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 072766	Shrink tubing III - Ø 4,8 – 12,0 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 071318	Shrink tubing I - Ø 1,6 – 4,8 mm
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 070717	Reduction nozzle 14 mm
EAN 4007841 006785	Pressure roller 40mm - Silicone
EAN 4007841 074210	ABS plastic welding rod
EAN 4007841 009601	Flexible hot air tool stand with suction pad foot
EAN 4007841 071417	Shrink tubing II - Ø 4,8 – 9,5 mm
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070915	Welding nozzle
EAN 4007841 009625	HL Light
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 070519	Reflector nozzle
EAN 4007841 009595	Flexible hot air tool stand with magnetic foot
EAN 4007841 034122	Pressure roller 40mm - Teflon
EAN 4007841 073411	PP plastic welding rod
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 071219	HDPE plastic welding rod
EAN 4007841 093211	Pressure roller 50mm - Rubber
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E
EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E