

Product data sheet

Item No. 92.052.8658.0

Male connector GST18I5F S2 R V PB02

Device connectors, snap-in panel mount, GST18i5, 5 pole, male, spring clamp connection, 250/400 V, 20 A, material thickness 0,5 - 1,5 mm, colour of coding: pastel blue



Item No.	92.052.8658.0
EAN	4015573583351
Order Unit	100 Piece(s)

Certificates / Approvals



Technical data

**General**

Rated current	20 A
Rated voltage	400 V
Pollution degree	2
Mechanical coding	Code 2
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Pastel blue
Marking of poles	

**Connection Data**

Connection cross section solid	2.5 mm <sup>2</sup>
Cross section solid 2	0.5 mm <sup>2</sup>
Connection cross section stranded	1.5 mm <sup>2</sup>
Cross section stranded 2	0.5 mm <sup>2</sup>
Terminations per pole	2

**Model**

Model	male
-------	------

Number of poles	5
Connection type	Tension clamp connection
Connecting thread metric	No thread
Angle of plug	Straight
Degree of protection (IP)	IP40
Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve
Thickness of housings (electrical device) 2	0.5 mm
Thickness of housings (electrical device)	1.5 mm
Built-in component	Snap-in

**Material**

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

**Dimensions**

Length	38 mm
Width	52.3 mm
Height	18.5 mm

**Technical drawing**

