

Precision scales PNS

KERN

Application:

Compact dimensions, advantageous in limited space

Execution:

- CAL calibration program for setting accuracy
- High-quality tuning fork weighing system for fast display of weighing value, precise dosing and high mechanical robustness
- Capacity indicator: an increasing bar graph display shows the remaining available weighing range
- Accurate counting: automatic reference optimisation gradually improves the average part weight
- Compact dimensions, advantageous in limited space
- Large, impact-resistant weighing tray made of stainless steel
- with robust tuning fork weighing system

Delivery:

with power supply unit and work protection hood



Art. no.	49000 053
Brand	KERN
Manufacturer Part Number	PNS 12000-1
Type description	PNS 12000-1
Max. weight measuring range	12000 g
Digit increment, weight	0.1 g
Plate size	190 x 190 mm
Material of cover panel	Stainless steel
With unit counting	Yes
Min. item weight	1 g
Reproducibility	0.1 g
Linearity	0.2 g
Settling time scale	3 s
Data transmission type	RS232
Housing dimensions (LxWxH)	196 x 293 x 89 mm
Display type	LCD
Gross Weight	3.700 kg
Product Group	447

EAN

4045761184008