

## “Nightwatchman“ LED machine light

IP 67, 140 mm



### Execution:

- High-performance LED in aluminium housing, rotatable
- Light temperature: cold white, approx. 5500 Kelvin, high-performance chip
- 120 degree uniform illumination, anti-glare and flicker-free, low-reflection
- Connection to 24 V machine controller or to 230 V power pack
- 2 x 43 mm rubber-coated magnets each with 85 N retention force.
- 3.0 W/400 lumen, 140x40 mm

### Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use

### Delivery:

including power pack



<b>Art. no.</b>	<b>56886 050</b>
<b>Brand</b>	BAUER & BÖCKER
<b>Manufacturer Part Number</b>	900/51
<b>Power rating</b>	3 W
<b>Length</b>	140 mm
<b>IP protection class</b>	IP 67
<b>Gross Weight</b>	0.762 kg
<b>Product Group</b>	5ID

### EAN

4260131235474