

## Aluminium step ladder, two-sided, clip-step R13

### Application:

Ladders for unlimited access/use. clip-step R13 tread cover for certified slip resistance on steps.

### Execution:

- Stable rectangular tube side-rails
- 80 mm deep, grooved steps
- 4-fold flanged step/side-rail connection
- Conical side-rail guide for a secure footing
- nivello® ladder shoes with patented 2-axis inclination technology
- ergo-pad® grip area with clamping mechanism
- 4-way bolted, solid aluminium ladder joint
- Two high-strength polyester straps to prevent spreading
- Step spacing: 235 mm
- Ladder inclination: 70°

### Advantage:

- clip-step R13 tread cover
- Maximum load: 150 kg



<b>Art. no.</b>	<b>59002 728</b>
<b>Brand</b>	MUNK GUENZBURGER STEIGTECHNIK
<b>Manufacturer Part Number</b>	41642
<b>Number of steps</b>	2 x 9
<b>Height</b>	2.08 m
<b>Working height</b>	3.6 m
<b>Pedestal width</b>	0.61 m
<b>Weight</b>	15.622 kg
<b>Accessibility</b>	Both sides
<b>Max. load capacity</b>	150 kg
<b>Step depth</b>	0.08 m
<b>Rail height</b>	73 mm
<b>Material</b>	Aluminium
<b>Width (bottom)</b>	0.61 m
<b>Transport width</b>	0.605 m
<b>Transport length</b>	2.24 m
<b>Transport depth</b>	213 mm
<b>Rail width</b>	25 mm
<b>Stride length</b>	1.71 m
<b>Gross Weight</b>	17.300 kg
<b>Product Group</b>	5AP

### EAN

4031405416420