

Sheet metal nibblers TruTool N 500

1400 watt



Application:

Ideal for removing tanks and containers. The nibbler cuts workpieces with bends of up to 90° and double metal sheets.

Advantage:

- The TruTool N 500 makes it possible to cut in all four cutting directions, even backwards.
- Vertical use (from top to bottom) requires very little force.
- Users can also pull the tool towards themselves in the horizontal plane, which is ideal for cutting coils, for example.

Delivery:

Punch 5/P5, die 5, in plastic case



Art. no.	71070 022
Model	TruTool N 500
Manufacturer Article Number	2574823
Max. cutting capacity in sheet metal (400 N/mm²)	5 mm
Max. cutting capacity in sheet metal (600N/mm²)	3.2 mm
Max. cutting capacity in sheet metal (800N/mm²)	2.5 mm
Max. cutting capacity in aluminium sheet (250 N/mm²)	7 mm
Cutting speed	1.5 m/min
Min. radius	90 mm
Power input	1700 W
Stroke rate	815
Weight	3.8 kg

EAN-Code

7640165438022