

Mini AC/DC current clamp CM P2

Accurate measurement of load currents up to 400 A

BENNING

Application:

For measurements in electrical installations and in service

Version:

- INRUSH measurement of motors and lighting systems
- Low pass filter (LPF, approx. 160 Hz) to suppress high-frequency pulses on clocked motor drives
- TRUE RMS

Advantage:

- Highest resolution of 10 mA in the 40.00 A range

Delivery:

Incl. Bag and batteries (2 x 1.5 V Micro/AAA/LR03)



Art. no.	75024 301
Model	CM P2
Display range	4200 digits
Measuring accuracy	+/- 1 %
Min./max. alternating current of measuring range	10 mA-400 A
Min./max. direct current of measuring range	10 mA-400 A
Continuity testing	No
Diode testing	No
Max. collet opening	23 mm
Memory function	HOLD
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT III/600 V
Length x width x height	149 x 59 x 28 mm

EAN-Code

4014651446793