

Pipe deburrer

for manual mode or electric drive



Application:

For quick and easy deburring in manual mode or for electric drive with 10-mm clamping range and maximum rotational speed 300 rpm, this solid all-metal tool comprises a deburring insert with four specially ground deburring blades and a driver. Suitable for exterior and interior deburring of stainless steel, steel, copper, brass, aluminium and plastic pipes 10-42 mm in diameter. To change between exterior and interior deburring, simply rotate the insert.

Execution:

- pipe deburrer, complete
- deburring insert with 4 ground deburring blades

Advantage:

- easy and quick deburring
- for interior or exterior deburring, simply rotate the insert



Art. no.	78233 010
Brand	REMS
Manufacturer Part Number	STÜCK-LISTE
Model	Pipe deburrer, complete
Min./max. workpiece diameter	10-42 mm
Locating pin diameter	10 mm
Max. rotation speed	300 rpm
Gross Weight	1.208 kg
Product Group	783