

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

JF


JIS Female Swivel
 JIS Dichtkopf
 Femelle JIS
 Femmina JIS
 Hembra loca JIS



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1S4JF4	1A4JF4	1A4JF4	G 1/4"				-4	53,2	29,8		4,2	19	19	
1S6JF6	1A6JF6	1A6JF6	G 3/8"				-6	59,2	33,9		6,7	22	22	
1S8JF8	1A8JF8	1A8JF8	G 1/2"				-8	66,3	36,6		9,6	27	27	
1S12JF12	1A12JF12	1A12JF12	G 3/4"				-12	73,3	43,1		15,5	32	36	
1S16JF16	1A16JF16	1A16JF16	G 1"				-16	83,6	49,2		20,7	41	41	
1S20JF20	1AP20JF20*	1AP20JF20*	G 1-1/4"				-20	102,1	58,1		26,6	50	46	
		1AT20JF20**	G 1-1/4"				-20	102,1	58,1		26,6	50	46	
1S24JF24	1A24JF24	1A24JF24	G 1-1/2"				-24	109,7	63,4		32,0	55	50	
1S32JF32	1A32JF32	1A32JF32	G 2"				-32	122,6	72,4		44,4	70	65	

KF

Komatsu Female Swivel
 Komatsu Dichtkopf
 Femelle Komatsu
 Femmina Komatsu
 Hembra loca Komatsu



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1S4KF4	1A4KF4	1A4KF4	M14x1,5				-4	56,1	32,7		4,2	19	19	
1S6KF6	1A6KF6	1A6KF6	M18x1,5				-6	60,4	35,1		6,7	24	22	
1S8KF8	1A8KF8	1A8KF8	M22x1,5				-8	69,5	39,8		9,6	27	27	
1S10KF10	1A10KF10	1A10KF10	M24x1,5				-10	75,4	46,0		12,4	1,25"	30	
1S10KF12	1A10KF12	1A10KF12	M24x1,5				-12	76,6	46,4		12,4	1,25"	30	
1S12KF12	1A12KF12	1A12KF12	M30x1,5				-12	81,5	51,3		15,5	36	36	
1S16KF16	1A16KF16	1A16KF16	M33x1,5				-16	91,4	57,0		20,7	41	41	
1S20KF20	1AP20KF20*	1AP20KF20*	M36x1,5				-20	113,4	69,4		26,6	46	46	
		1AT20KF20**	M36x1,5				-20	113,4	69,4		26,6	46	46	
1S24KF24	1A24KF24	1A24KF24	M42x1,5				-24	120,5	74,2		32,0	55	50	

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice