


Adapter for MSC-D, 25 A

Part no. MSFAD-25
Catalog No. 191097
Eaton Catalog No. MSFD-25




Delivery program

Product range			Accessories
Accessories			Busbar adapters
			Approved to UL 508
Rated operational voltage	U_e	V	690
Rated operational current	I_e	A	25
Terminal capacity			AWG 12 (4 mm ²)
Adapter width		mm	45
Adapter length		mm	160
DIN rail		Quantity	1
For use with			MSC-D, 25 A

Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Busbar adapter (EC001531)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Busbar trunking system (LV circuitry) / Busbar adapter (low-voltage switching technology) (ecl@ss8.1-27-37-03-04 [ACN951008])			
Mounting rail armament			1 mounting rail
Type of electrical connection			Round conductor
Rated current I_n		A	25
Min. busbar thickness		mm	2
Max. busbar thickness		mm	2
Width of the adapter		mm	45
Rail width		mm	24
Busbar distance		mm	60

Dimensions



Additional product information (links)

Motor starters and "Special Purpose Ratings" for the North American market

http://www.moeller.net/binary/ver_techpapers/ver953en.pdf

Busbar Component Adapters for modern Industrial control panels

http://www.moeller.net/binary/ver_techpapers/ver960en.pdf