

BOX TERMINAL 3 PCS. ACCESSORY FOR: 3VA4/5 125

| Model | |
|---------------------|-------------|
| Product brand name | SETRON |
| Product designation | accessories |

| Connections according IEC | |
|--|--|
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / solid / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / solid / maximum | 16 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / maximum | 50 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 70 mm ² |
| Wire stripping length | 12 mm |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • solid | <= 16 mm ² : 5 Nm |
| <ul style="list-style-type: none"> • stranded | <= 16 mm ² : 5 Nm, >= 25 mm ² : 8 Nm |
| <ul style="list-style-type: none"> • finely stranded | <= 16 mm ² : 5 Nm, >= 25 mm ² : 8 Nm |

| Connections according UL | |
|--|--|
| Wire stripping length | 0.5 in |
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / solid / minimum | 14 AWG |
| <ul style="list-style-type: none"> • for copper cable / solid / maximum | 10 AWG |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 14 AWG |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 3/0 AWG |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / minimum | 14 AWG |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / maximum | 3/0 AWG |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • solid | <= 10 AWG: 45 lb-in |
| <ul style="list-style-type: none"> • stranded | <= 6 AWG: 45 lb-in, >= 4 AWG: 70 lb-in |
| <ul style="list-style-type: none"> • finely stranded | <= 6 AWG: 45 lb-in, >= 4 AWG: 70 lb-in |

Certificates

| General Product Approval | EMC | Declaration of Conformity | other |
|--|---|---|--|
|  CSA |  UL |  |  RCM  EG-Konf. Miscellaneous |

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JA11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JA11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JA11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

08/28/2017