

MAX001T

- Waterproof and dustproof IP67 certified
- Four compartments
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system

Body: polypropylene random

Latches: nylon

O-Ring: polymer

COLOURS: transparent

EXTERNAL DIMENSIONS: 175 x 115 x H47mm (6.88 x 4.52 x H1.85 inch)

INTERNAL DIMENSIONS: 157 x 82 x H41mm (6.18 x 3.22 x H1.61 inch)

LID-BOTTOM DEPTH: 12+29mm (0.47+1.14 inch)

WEIGHT: 0.16 kg – 0.352 lbs.

CARTON DIMENSIONS: 260 x 190 x 300mm – 10.24 x 7.48 x 11.81 inch

PCS PER CARTON: 12

WEIGHT OF THE FULL CARTON: 1.95kg – 4.30 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -10 / 80°C (14 / 176°F)

CUSTOMIZATION: personalized nameplate/resin label

FEATURES: IP67

