



**FEATURES:**

- ✓ Fits standard banana jack

**MATERIALS:**

- Banana Plug Body: Brass, Alloy 360, 1/2 Hard
- Spring: Beryllium Copper, Berylco 25, Cond. H.T.
- Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches
- Screw: Model 3265 - 6-32 x .25" (6,35mm) Pan head, Phillips, steel, nickel plated  
 Model 3266 - 8-32 x .25" (6,35mm) Pan head, Phillips, steel, nickel plated.
- Solder Lug: Copper per QQ-C-576
- Finish: Electro tin plated

**RATINGS:**

- Voltage: Hands free testing in controlled voltage environments: 500 Vrms Max. *For CE compliance: not intended for hand-held use at voltages above 33 Vrms/70 Vdc.*
- Current: 15 Amps

**ORDERING INFORMATION:**

- Model with 6-32 screw: 3265
- Model with 8-32 screw: 3266
- Sold in package of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
 All specifications are to the latest revisions. Specifications are subject to change without notice.  
 Registered trademarks are the property of their respective companies.