

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201000001](#)
Status: **Active**
Overview: PROFIBUS Solutions
Description: Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Female

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	120100
IP Rating	IP67
Material - Contact	Brass
Overview	PROFIBUS Solutions
Product Name	Micro-Change (M12), PROFIBUS
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	78678850053

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Reverse
Material - Connector Body	N/A
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	51.255/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	22

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Material Info

Engineering Number	BA5S00-32
--------------------	-----------

Reference - Drawing Numbers

Sales Drawing	1201000001-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120100 Series](#)