

Forklift truck, short version

Nylon single fork rollers, rubber steering wheels

Application:

Especially suitable for confined spaces and lorries.

Execution:

- Industrial version: Torsion-free single-shell frame and forks
- Robust steel tube drawbar with counter bearing for pushing operation
- Rubber-encased handle
- Control lever for raise/move/lower functions
- Hydraulic hand pump, maintenance-free mounting
- Full lock: 2 x 100°

Art. no.	50262 460
Brand	FETRA
Fork roller diameter	80 mm
Manufacturer Part Number	2 118
Material	Steel
Load-carrying capacity	2500 kg
Fork length	800 mm
Fork arm width	160 mm
Fork, external distance	540 mm
Min. lift height	85 mm
Lift height	200 mm
Fork castor design	Single
Material of fork castor	Nylon
Castor-wheel diameter	200 mm
Material of steering wheels	Rubber
Colour	Melon yellow RAL 1028
Surface	Powder-coated
Gross Weight	66.000 kg
Product Group	5AE



EAN

4017976021188