

## SPANNFIX 4.0 ball joint vice 100-mm jaw width

Screw-on clamping foot



### Application:

Facilitates a range of working processes in precision engineering, laboratories, testing fields and all electronic/mechanic workshops.

### Execution:

- Clamping pressure/clamping force: 12,000 N
- Table top thickness: up to max. 80 mm, working radius: 330 mm (from centre of ball)
- Cast aluminium with chromed steel parts,
- Colour: textured powder coat in metallic dark grey
- With clamping pins, replaceable clamping jaws, centring eye and outstanding ball clamping force
- The four clamping horns adapt to the shape and size of the product. They can be rotated on their axis and keep a firm grip on every object. The centring eye ensures that the work is perpendicular
- Screw-on clamping foot

### Advantage:

- Quick, flexible mounting of the vice on the workbench with no damaged sustained
- Vice can be rotated by 360° to all sides and swivelled by 90° thanks to firmly integrated ball joint



<b>Art. no.</b>	<b>51056 081</b>
<b>Brand</b>	BERNSTEIN
<b>Manufacturer Part Number</b>	9-290
<b>Vice design</b>	Screw-on clamping foot
<b>Jaws width</b>	100 mm
<b>Min./max. clamping width</b>	0-100 mm
<b>Clamp in depth</b>	50 mm
<b>Colour</b>	Grey
<b>Gross Weight</b>	5.500 kg
<b>Product Group</b>	515

### EAN

4250838515771