



# Charger & Maintainer 6V/12V – 4 Amp

EAN : 542503 853129 9

SKU : BXAE00022

- Charge & maintenance functions
- Maximum current 4 Amp
- Suitable for 6V/12V batteries
- Manual voltage selection
- Up to 8 steps intelligent charging cycles
- No battery removal required
- For all types of lead-acid batteries
- Supplied with clamps and eyelets



## SPECIFICATIONS

INPUT	Voltage	220 - 240 Volt AC 50 - 60Hz			
	Plug	EU	Type	Standard	
OUTPUT	Nominal Voltage	6V - 12V	Max Output	4A	
	Cable length	1,5m + 0,5m clamps cable and O-rings cable			
	Terminals	Clamps and O-rings			
CAPACITY	Charge	4 - 80 Ah	Maintain	4 - 120 Ah	
	Recovery	YES			
	Compatibility	Lead Acid battery : AGM , GEL, VLRA, WET, LIQUID			
INTERFACE	LED	Charging status - Error Indicator			
	MMI	Output voltage and vehicle battery's selection			
IP CLASSIFICATION	IP 65				
CERTIFICATION	CE EN60335 - 2 - 29 - LVD - EMC - RoHS				

SKU	EAN code	5425038 53129 9				
	Length	151mm	Width	59mm	Height	233mm
	Gross weight	790gr	Net weight	610gr		
Carton box	EAN code	2 5425038 53129 3				
	Length	483mm	Width	210mm	Height	171mm
	Gross weight	4,90kg	Net weight	3,66kg		
	Qty of SKUs per carton box	6				
PALLET	EAN code	4 5425038 53129 7				
	Length	120cm	Width	80cm	Height	135cm
	Gross weight	267kg	Net weight	179kg		
	Carton per layer	7	Qty of layers	7	Cartons per pallet	49
	Qty SKUs per pallet	294				
	type of pallet	Plywood pallet				