

Blacklight BL368 Linear T12

F40W T12 BL368 48
0000099



Product features

- Blacklight BL368 Linear T12



PRODUCT OVERVIEW

Product name	F40W T12 BL368 48
Technology	Special applications
Lamp shape	Tubular shape
Type	T12
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
ETIM Class	EC002962
E-number FI	4940428
Light colour	BL368 Blacklight
Wattage (W)	40.00
Dimmable	No
Average life (Nominal) (h)	10000
Product EAN number	5410288000992

DATA TABLE

General data

Product name	F40W T12 BL368 48
Technology	Special applications
Lamp shape	Tubular shape
Type	T12
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
Operating temperature range (°C)	-20°C - 40°C
ETIM Class	EC002962
E-number FI	4940428

Blacklight BL368 Linear T12

F40W T12 BL368 48

0000099

Optical data

Ambient temperature for maximum luminous flux (°C)	25
Light colour	BL368 Blacklight
Adjustable chromaticity	N

Electrical data

Wattage (W)	40.00
Mains voltage (V)	230-240V
Control gear required	Yes
Transformer required	No
Dimmable	No

Lifetime data

Average life (Nominal) (h)	10000
----------------------------	-------

Physical data

Nominal Product Length (mm)	1200.0
Nominal Product Diameter (mm)	38
Max. Length base to base (mm) - A	1199.4
Length base to pin Min-Max (mm) - B	1204.1-1206.5
Max. Lamp Length (mm) - C/L	1213.6
Max. Lamp Diameter (mm) - D	40.5
Weight (kg)	0.275

Packaging


Single packaging type	Carton
Product EAN number	5410288000992
Packaging single length / height (cm)	121.2
Packaging single width (cm)	4.3
Packaging single depth (cm)	4.1
DUN14 (outer)	15410288000999
Units per outer package	25
Packaging outer length / height (cm)	124.0
Packaging outer width (cm)	22.0
Packaging outer depth (cm)	21.0

Safety data

Lamp mercury content (mg)	9.00
Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Intended purpose	Flykilling - Insect attraction
Suitable for household illumination	No
Safety message	Not suitable for household

Blacklight BL368 Linear T12 F40W T12 BL368 48 0000099

PHOTOMETRY



TECHNICAL DRAWINGS

