

## HTI 250 W/32 C

HTI | Metal halide lamps with reflector



### Areas of application

- Medical endoscopy
- Industrial boroscopy
- Light guide systems in the entertainment sector

### Product benefits

- Highly efficient lighting systems for injecting light into a light guide

### Product features

- Short-arc lamps with dichroic focusing reflector



# Product datasheet

## Technical data

### Electrical data

Nominal wattage	250.00 W
Nominal voltage	45 V
Nominal current	6 A
Lamp current	6.00000 A


### Photometrical data

Color temperature	5600 K
-------------------	--------

### Light technical data

Focal length	32.0 mm
--------------	---------

### Dimensions & weight



Diameter	67.0 mm
Length	73.0 mm

### Lifespan

Lifespan	250 h
----------	-------

### Additional product data

Footnote only for product	With connecting cable and plug contact
---------------------------	--

### Capabilities

Burning position	p15/s15
------------------	---------

### Certificates & standards

EEI – Energy Label	B
--------------------	---

## Product datasheet

---

### Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300021805	OSRHTI25032C	-	-	-

## Product datasheet

---

### Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, HTI lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300021805	HTI 250 W/32 C	Folding carton box 1	103 mm x 87 mm x 87 mm	0.78 dm <sup>3</sup>	153.00 g
4050300248820	HTI 250 W/32 C	Shipping carton box 2	186 mm x 121 mm x 100 mm	2.25 dm <sup>3</sup>	352.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---