



Audible & Visual Alarms

Technische Daten / <i>technical data:</i>		B/SM-28
Spannungsbereich / <i>operating voltage</i> (VDC)		10-30
Stromaufnahme / <i>current consumption</i> (mA)		< 30
Tonanzahl / <i>signalling tones</i> (2 Ton ansteuerbar / <i>2 tone selectable</i>)		28
Lautstärke / <i>sound pressure level (SPL)</i> (dB / 1m)		96-113
Lautstärkeregelung / <i>volume control</i> (dB)		-20
Schutzklasse / <i>ingress protection</i>		IP 54
Abmessungen / <i>dimensions</i> (mm)	Flange Version	Ø 57 x 85 x 51
	UP Version (with connector)	86 x 86 x 49
	AP Version	86x 86 x 56.5
Gehäusefarbe(n) / <i>housing colour(s)</i> (RAL 3001)		Rot / <i>red</i>
	(RAL 9010)	Weiß / <i>white</i>

