

Wiha bit holder.

For rapid changing of bits without tools.



CentroFix bit holders are characterised by particular user friendliness.

The bit is automatically locked when it is inserted. When unlocked it moves forward several millimetres and can be removed easily.

Ideal for powerful users- the CentroFix Force was designed to be particularly stable. The CentroFix SuperSlim shows off its thin design.

The new MagicFlip Force is perfectly suited for hard jobs thanks to its robust operating sleeve of steel. With its strong Neodym ring magnet it even securely holds heavy screws.



Wiha CentroFix Force

- Suitable for all bits with 1/4" hex drive Style C6.3 and E6.3
- Operating sleeve of robust, hardened steel
- SelfLock
The bit is locked mechanically and held securely when inserted
- EasyOut
When unlocked, the bit moves into the ideal removal position



Wiha CentroFix Super Slim

- Up to 30% reduced outer diameter compared to "conventional" quick release holders
- Screw accessibility is better in confined holes
- SelfLock
The bit is locked mechanically and held securely when inserted
- EasyOut
When unlocked, the bit moves into the ideal removal position



Wiha MagicFlip Force

- Extremely strong Neodym ring magnet, holding force 16N (approx. 1.6 Kg)
- New – also suitable for drywall screws with small screw heads
- New – operating sleeve of robust steel
- FlipBack
the operating sleeve automatically springs back during recessing.
- Magnet On/Off
The ring magnet can be "deactivated" by pushing the operating sleeve back

Wiha Bit holder with handle.

Bit holder 1/4".



384 Bit holder with handle, magnetic, 1/4".

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
 Handle: Wiha SoftFinish® multi-component handle with roll-off protection.
 Bit holder: Stainless steel with strong magnet.
 Suitable for: For bits according to DIN 3126, ISO 1173 style C 6.3.

Order-No.	Ø	↔	↔	↕	↔
01475	1/4	125	225	36	10
01476	1/4	300	400	36	5



386 Bit holder with handle, flexible shaft, 1/4".

Blade: Plastic coated flexible metal.
 Handle: Wiha SoftFinish® multi-component handle with roll-off protection.
 Bit holder: With retaining ring.
 Suitable for: For bits according to DIN 3126, ISO 1173 style C 6.3.
 Application: For offset screws.

Order-No.	Ø	↔	↔	↕	↔
01479	1/4	150	268	36	10



387 Bit holder with handle, quick release holder, 1/4".

Handle: Wiha SoftFinish® multi-component handle with roll-off protection.
 Bit holder: ClicFix quick release holder, magnetic.
 Suitable for: For bits according to DIN 3126, ISO 1173 style C 6.3.
 Application: Compact, handy style for working in confined spaces.
 For applications where the bit must be held tight.

Order-No.	Ø	↔	↔	↕	↔
25874	1/4	35	146	30	10



281-02 Bit holder with handle, magnetic, 1/4".

Handle: Wiha SoftFinish® multi-component handle with roll-off protection.
 Bit holder: Stainless steel with strong magnet.
 Suitable for: For bits according to DIN 3126, ISO 1173 style C 6.3 and E 6.3.
 Application: Compact screwdriver together with bits, 1/4".
 Together with Wiha countersink bits, can be used as manual deburrer.

Order-No.	Ø	↔	↕	↔
32160	1/4	125	36	10

Bit holder 1/4".



281 01 Bit holder with handle, magnetic, 1/4".

Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.
 Bit holder: Stainless steel with strong magnet.
 Suitable for: For bits according to DIN 3126, ISO 1173 style C 6.3.
 Application: For working in confined spaces.
 Extra: Together with Wiha countersink bits, can be used as manual deburrer.

Order-No.	Ø	↔	↕	↔
29463	1/4	57	34	10



281-01ESD ESD bit holder with handle, retaining ring, 1/4". Dissipative handle, ESD-safe.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Surface resistance $10^6 - 10^9$ ohms.
 Universal use for all bits.
 Standards: Handle: IEC 61340-5-1.
 Output: For bits according to DIN 3126, ISO1173 style C 6.3.
 Bit holder: Stainless steel with retaining ring.
 Application: For working on electrostatically sensitive components, especially in tight places.

Order-No.	Ø	↔	↕	↔
32484	1/4	57	34	10



387ESD ESD bit holder with handle, quick release holder, 1/4". Dissipative handle, ESD-safe.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Surface resistance $10^6 - 10^9$ ohms.
 Standards: Handle: IEC 61340-5-1.
 Output: For bits according to DIN 3126, ISO1173 style C 6.3, E 6.3 and double bits.
 Input: DIN 3126, ISO 1173, style E 6.3.
 Bit holder: Stainless steel with retaining ring.
 Application: For working on electrostatically sensitive components.
 With integrated CentroFix bit holder, suitable for all bits and bit drills with the style C 6.3, E 6.3 or double bits.
 Extra: True single-handed operation, extremely high retention force of bits (up to 20 kg) and virtually no play between bit and holder thanks to special closing and holding mechanism.

Order-No.	Ø	↔	↔	↕	↔
32161	1/4	38	148	30	10