



Main

Range of product	Modicon Rectified
Product or component type	Power supply
Power supply type	Rectified and filtered
Rated power in W	480 W
Input voltage	400 V AC three phase, terminal(s): L1, L2, L3
Output voltage	24 V DC
Power supply output current	20 A
Anti-harmonic filter	Low frequency harmonic currents
Product certifications	EAC KC UL 508 cULus

Complementary

Network frequency limits	47...63 Hz
Input voltage limits	360...440 V
Cos phi	0.81 at 400 V
Efficiency	78 %
Power dissipation in W	105 W
Output coupling	Parallel Series
Output protection type	Against overvoltage, protection technology: 2 J peak limiter Against overload and short-circuits, protection technology: external fuse, 25 A
Holding time	6 ms
Status LED	1 LED (green) output voltage
Connections - terminals	For input ground connection: screw type terminals, connection capacity: 1 x 2.5...1 x 4 mm ² AWG 14...AWG 11 For input connection: screw type terminals, connection capacity: 9 x 2.5...9 x 4 mm ² AWG 14...AWG 11 For output connection: screw type terminals, connection capacity: 4 x 10...4 x 16 mm ² AWG 8...AWG 6
Depth	213.0 Mm
Height	102.0 Mm
Width	220 Mm
Net weight	9.79 Kg
Compatibility code	ABL8T

Environment

IP degree of protection	IP20 conforming to EN/IEC 60529
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % without condensation or dripping water
Operating altitude	3000 m
Electrical shock protection class	Class I conforming to VDE 0106-1
Dielectric strength	2000 V between input and ground 4600 V between input and output 500 V between output and ground
Environmental characteristic	EMC conforming to IEC 62041 Safety conforming to EN/IEC 61558-2-6 Safety conforming to UL 508 Safety conforming to UL 60950-1 EMC conforming to EN/IEC 61000-3-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10.988 Kg
Package 1 Height	36.8 Cm
Package 1 width	32.6 Cm
Package 1 Length	16.4 Cm
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Weight	140.0 Kg
Package 2 Height	75.0 Cm
Package 2 width	80.0 Cm
Package 2 Length	120.0 Cm


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
220	215	104	200	80	8


Dimensions in in.

a	b	c	G	J	Ø
8.66	8.46	4.09	7.87	3.15	0.31

Internal Wiring Diagram



Load Limits Curve



- (1) Nominal line supply + 10%
- (2) Nominal line supply
- (3) Nominal line supply - 10%

Product Life Status : **Commercialised**