


E12333



Connecting cable with plug

ASTGH040MSS0010C04



Application	
Special feature	Free from silicone; Halogen-free; Gold-plated contacts; Screened cable
Free from silicone	yes
Electrical data	
Operating voltage [V]	< 50 AC / < 60 DC
Protection class	III
Max. current load total [A]	4
Operating conditions	
Ambient temperature [°C]	-25...90
Protection	IP 68
Mechanical data	
Weight [g]	386.2
Dimensions [mm]	14.5 x 14.5 x 48.4
Materials	PUR
Material nut	diecast zinc, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 10 m, PUR, Halogen-free, black, Ø 5 mm, shielded; 4 x 0.34 mm ² (42 x Ø 0.1 mm)	
Electrical connection - plug	
Connector: 1 x M12, straight; Moulded body: PUR; Locking: diecast zinc, nickel-plated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm; Shielded connection cable: screen not connected	

E12333




Connecting cable with plug

ASTGH040MSS0010C04



Connection



Core colours :

BK =	black
BN =	brown
BU =	blue
WH =	white