

Product characteristics

Splitter box

Terminals

Free from silicone

Gold-plated contacts

Electrical data

Electrical design

Operating voltage [V]

Max. total current load [A]

Max. current load per location [A]

Environment

Ambient temperature [°C]

Ambient temperature (moving) [°C]

Protection

Mechanical data

Design

Material body

Material nut

Tightening torque for knurled nut [Nm]

Weight [kg]

Electrical connection

Connection

Wiring

DC

10...30 DC

12

2

-25...80

-5...60

IP 67

8 way

housing: PBT-GF 30



socket: stainless steel 316L / 1.4404

0.8...1.5 *)

0.368

19 terminals; cable gland PG11

EBT005 - Splitter box - eclass: 27279219 / 27-27-92-19



Accessories	
Accessories (included)	2 protective caps; 10 labels; assembly tool for cage clamps
Remarks	
Remarks	*) Take into account the maximum value of the counterpart!
Pack quantity [piece]	1
Other data	
Ports	M12