



Generic code	Rubix engineering code	G	l	D	d1	m	c	b	t	Weight (kg)
ZMA15/33-AKN	891383	M 15x1	16	33	28	M5	8.0	4	2.0	0.08
ZMA20/38-AKN	891384	M 20x1	20	38	33	M5	10.0	5	2.0	0.12
ZMA20/52-AKN	891385	M 20x1	25	52	47	M5	12.5	5	2.0	0.32
ZMA25/45-AKN	891386	M 25x1.5	20	45	40	M6	10.0	5	2.0	0.16
ZMA25/58-AKN	891387	M 25x1.5	28	58	52	M6	14.0	6	2.5	0.43
ZMA30/52-AKN	891388	M 30x1.5	22	52	47	M6	11.0	5	2.0	0.22
ZMA30/65-AKN	891389	M 30x1.5	30	65	59	M6	15.0	6	2.5	0.55
ZMA35/58-AKN	891390	M 35x1.5	22	58	52	M6	11.0	6	2.5	0.26
ZMA35/70-AKN	891391	M 35x1.5	30	70	64	M6	15.0	6	2.5	0.61
ZMA40/62-AKN	891392	M 40x1.5	22	62	56	M8	11.0	6	2.5	0.27
ZMA40/75-AKN	891393	M 40x1.5	30	75	69	M8	15.0	6	2.5	0.67
ZMA45/68-AKN	891394	M 45x1.5	24	68	62	M8	12.0	6	2.5	0.35
ZMA45/85-AKN	891395	M 45x1.5	32	85	78	M8	16.0	7	3.0	0.92
ZMA50/75-AKN	891396	M 50x1.5	25	75	68	M8	12.5	6	2.5	0.43
ZMA50/92-AKN	891397	M 50x1.5	32	92	84	M8	16.0	8	3.5	1.06
ZMA55/98-AKN	891398	M 55x2	32	98	90	M8	16.0	8	3.5	1.17
ZMA60/98-AKN	891399	M 60x2	32	98	90	M8	16.0	8	3.5	1.07
ZMA65/105-AKN	891400	M 65x2	32	105	97	M8	16.0	8	3.5	1.21
ZMA70/110-AKN	891401	M 70x2	35	110	102	M8	17.5	8	3.5	1.40
ZMA75/125-AKN	891402	M 75x2	38	125	117	M8	19.0	8	3.5	2.11
ZMA80/120-AKN	891403	M 80x2	35	120	105	M8	17.5	8	4.0	1.33
ZMA90/130-AKN	891404	M 90x2	38	130	120	M8	19.0	10	4.0	2.01
ZMA90/155-AKN	891405	M 90x2	38	155	146	M8	19.0	10	4.0	3.36
ZMA100/140-AKN	891406	M 100x2	38	140	128	M10	19.0	12	5.0	2.23