




L60 Series 0.230" (5.9mm) Water Tight LED Panel Mount Indicator



L60 Series offers a robust body with drip-proof protection in a small package

Applications

- Automotive
- Aerospace
- Industrial
- Instrumentation
- Medical
- Military
- Mining
- Outdoor
- Safety
- Transportation
- Vending & Gaming Machines

Key features

- Water Tight
- Tinted Diffused LEDs
- Reflective Chrome-Plated Body
- 45° Viewing Angle
- Mounting Hardware Provided
- 6" (152.4mm) Wire Leads, 24 AWG
- Mounting Hole 0.232" \pm 0.003" (5.9mm \pm 0.1mm)
- Maximum Panel Thickness 0.070" (1.7mm)
- RoHS Compliant

Product specifications

VCC Model Number	Output Color	Design Voltage / Current (Vf/If)	Max. Voltage / Current (Vf/If)	Typical Intensity (mcd)	Peak Wavelength (nm)
L60D-R5-W	RED	5VDC / 17mA	5.5VDC / 20mA	60	635
L60D-A5-W	AMBER	5VDC / 17mA	5.5VDC / 20mA	30	583
L60D-G5-W	GREEN	5VDC / 17mA	5.5VDC / 20mA	44	565
L60D-R12-W	RED	12VDC / 16mA	14VDC / 19mA	60	635
L60D-A12-W	AMBER	12VDC / 16mA	14VDC / 19mA	30	583
L60D-G12-W	GREEN	12VDC / 16mA	14VDC / 19mA	44	565
L60D-R28-W	RED	28VDC / 15.8mA	30VDC / 17.5mA	60	635
L60D-A28-W	AMBER	28VDC / 15.8mA	30VDC / 17.5mA	30	583
L60D-G28-W	GREEN	28VDC / 15.8mA	30VDC / 17.5mA	44	565

Dimensions

