




Your Global Partner in Lighting Solutions

MINIATURE LAMP 7219



Part #	7219				
Description	T1 W.T. 12V .06A .15CP				
Bulb Shape	T-1	Filament	C-2F	Base Style	Wire Terminal
Glass Diameter (in)	0.12	MOL [†] (in)	0.250	LCL ^{††} (in)	0.13
Glass Diameter (mm)	3	MOL (mm)	6.35	LCL (mm)	3.18
Volts	12	MSCP ‡	0.15	Avg Life Hrs	10000
Watts	0.72	Amps	0.06	RoHS Compliant	
E-Marked	No	Drawing		New Announcement	

Click below to see NAFTA & Packaging information



† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.

CERTIFICATES

APPLICATION GUIDES

DOWNLOADS

ABOUT



[List of PDF downloads](#)



[About Us](#)
[Contact Us](#)
[Site Map](#)

CONTACT

CEC INDUSTRIES, LTD
599 Bond Street
Lincolnshire, IL 60069
Phone: (847) 821-1199
Toll Free: (800) 572-4168
Fax: (847) 821-1133

www.cecindustries.com

