

## Product information

# 90 25 20

## Pipe Cutter

For composite pipes and protective tubes

- For cutting composite pipes Ø12.0 to 25.0 mm and for cutting flexible protective tubes Ø 18.0 - 35.0 mm without damaging a potential pipe inside
- A calibration arbor can be fitted, for example for Geberit composite pipes with Ø 11.5 and 15.0 mm
- Blades: special tool steel, oil-hardened, interchangeable
- Tool body: high-grade chrome vanadium electric steel, oil-hardened



MM

General	
Article No.	90 25 20
EAN	4003773046004
Pliers	galvanized
Handles	with multi-component grips
Weight	332 g
Dimensions	210 x 70 x 20 mm
Reach	yes
RohS	no
Technical details	
Cutting capacities composite pipes (diameter)	Ø 12 – 25 mm
Blade length	25 mm
Cutting capacities protective tubes (diameter)	Ø 18 – 35 mm
Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006
UNSPSC 13.1	23151901
Spare Parts	
90 29 01	Spare blade for 90 25 20 / 90 10 185 / 90 25 185,
90 29 02	1 pair of spare blades for 90 25 20 (protective pipes),
90 29 15	Calibration arbor for 90 25 20 (Geberit pipes),
90 29 20 01	Spring for 90 25 20,
90 29 20 02	Plastic jaw covers for 90 25 20,

technical change and errors excepted



Clean cut of protective tubes Ø 18 - 35 mm



Composite pipes of Ø 12 - 25 are cut cleanly and without deformation