

Sylmaster T5 - PL Louvre

FHE 16 2x28W G5
0055720



Product features

- Sylmaster T5 - PL Louvre



PRODUCT OVERVIEW

Product name	FHE 16 2x28W G5
Technology	Fluorescent
Cap/Base	G5
Housing	Steel
Mount	Ceiling surface mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number SE	7098464
E-number Norway	3306306
Warranty	2 years
Fixture luminous flux (lm)	3380
Luminaire efficacy (lm/W)	106
LOR (%)	65
Light colour	N/A
Light source included	Fixture without Lightsource
Total power consumption (W)	32
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	No
Housing colour	White
IP rating	IP20
IK rating	IK07
Product EAN number	5410288557205

DATA TABLE

General data

Product name	FHE 16 2x28W G5
Technology	Fluorescent
Cap/Base	G5
Housing	Steel
Mount	Ceiling surface mounting

Sylmaster T5 - PL Louvre

FHE 16 2x28W G5
0055720

Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number SE	7098464
E-number Norway	3306306
Warranty	2 years

Optical data

Fixture luminous flux (lm)	3380
Luminaire efficacy (lm/W)	106
LOR (%)	65
Light colour	N/A
Adjustable chromaticity	N

Electrical data

Light source included	Fixture without Lightsource
Total power consumption (W)	32
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Dimmable	No
Glow Wire Test (°C)	960
Nominal Frequency (Hz)	50/60Hz

Physical data


Housing colour	White
IP rating	IP20
IK rating	IK07
Nominal Product Length (mm)	1250
Nominal Product Width (mm)	202
Nominal Product Height (mm)	85
Weight (kg)	4.65

Packaging

Single packaging type	Carton
Product EAN number	5410288557205
Packaging single length / height (cm)	126.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	21.0
DUN14 (outer)	05410288557205
Units per outer package	1
Packaging outer length / height (cm)	126.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	21.0

Sylmaster T5 - PL Louvre FHE 16 2x28W G5 0055720

PHOTOMETRY



TECHNICAL DRAWINGS

Dimensions (mm)					
Dim.	L	I	H	F	Mounting depth
1028	150	20	85	1000	5
2128	150	20	85	1000	5

