

Pneumatic grease gun with nozzle pipe and mouthpiece

Model DFP 500, for use with 400-ml cartridges



Application:

For simple lubrication, using 400-g grease cartridges or loose grease.

Execution:

- Single-handed operation
- Pressure ratio 1:60
- Max. operating pressure: 420 bar
- Input pressure: min. 2 to max. 7 bar
- Recommended air pressure: 6 bar
- With hydraulic nosepiece
- Nozzle pipe or high-pressure hose connection: M10x1

Advantage:

- With 150-mm nozzle tube, even hard-to-reach lubrication areas are easy to access



Art. no.	56266 010
Brand	SAMOA-HALLBAUER
Manufacturer Part Number	10205
Volumetric capacity	500 ml
Connection thread	MT G 1/8 inch
Feed volume per stroke	1 cm ³
Gross Weight	2.136 kg
Product Group	5IG

EAN

4024937102053

