

## Pneumatic grease gun with nozzle pipe and mouthpiece

Model DFP 500, for use with 400-ml cartridges



### Application:

For simple lubrication, using 400-g grease cartridges or loose grease.

### Version:

- Single-handed operation
- Pressure ratio 1:60
- Max. operating pressure: 420 bar
- Input pressure: min. 2 to max. 7 bar
- Recommended air pressure: 6 bar
- With hydraulic nosepiece
- Nozzle pipe or high-pressure hose connection: M10x1

### Advantage:

- With 150-mm nozzle tube, even hard-to-reach lubrication areas are easy to access



<b>Art. no.</b>	<b>56266 010</b>
<b>Volumetric capacity</b>	500 ml
<b>Connection thread</b>	MT G 1/8 inch
<b>Feed volume per stroke</b>	1 cm <sup>3</sup>

### EAN-Code

4024937 102053