

Pneumatic drill 9030N-1

375 W



Application:

Ideal for bodywork and industry

Advantage:

- Suitable for continuous operation

Delivery:

incl. coupling connector: Nominal width 7.2



Art. no.	75032 211
Model	9030N-1
Max. idle speed	2000 rpm
Power rating	373 W
Air consumption	113 l/min
Connection thread	IT 1/4 inch
Min./max. drill chuck span width	1-10 mm
Inner hose diameter	10 mm
Weight	1 kg
With right/left-hand rotation	Yes
Operating pressure	6.3 bar
Length	195 mm
Sound-pressure level	88.7 dB
Noise level	96 dB

EAN-Code

4000896206377