

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010011064](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: 5.08mm Pitch KK Crimp Terminal Housing, 6 Circuits, Natural

Documents:

3D Model	Product Specification PS-99020-0087-001 (PDF)
3D Model (PDF)	Packaging Specification 30010001-PK-000 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	3001
Application	Power, Wire-to-Board
Overview	KK 508 Connector System
Product Name	KK 508
UPC	800753613089

Physical

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1.830/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	WAVE
-----------------------------	------

Material Info

Engineering Number	3001-06
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	30010001-PK-000
Product Specification	PS-99020-0087-001
Sales Drawing	SDE-3001-N-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3001](#) Series

Mates With

Headers [3061](#) , [3003](#) , [3061](#)

Use With

Crimp Terminals [2478](#) , [2578](#) , [2878](#)