


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2063960001](#)  
**Status:** **Active**  
**Overview:** [L1NK Connector System](#)  
**Description:** L1NK 300 Female Crimp Terminal, 18-20 AWG, Tin (Sn) Plating, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2092080000-TS-000 (PDF)</a>
<a href="#">Product Specification 2092080000-PS-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 2092080000-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification 2063960000-PK-000 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	<a href="#">206396</a>
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<a href="#">L1NK Connector System</a>
Product Name	L1NK 300
UPC	193264185849

**Physical**

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.100/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.42mm-2.10mm
Wire Size AWG	18, 20
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	11.0A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2092080000-AS-000
Packaging Specification	2063960000-PK-000
Product Specification	2092080000-PS-000
Sales Drawing	2063960000-SD-000
Test Summary	2092080000-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[206396](#) Series

**Use With**

L1NK 300 Receptacle Housing [209209](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Crimp Tool for	<a href="#">2002189600</a>
L1NK300 Receptacle Terminal, 18-20 AWG, UL1007 and UL1061 Wires	
FineAdjust Applicator	<a href="#">2037026600</a>
for L1NK300 Receptacle Terminal, 18-20 AWG Wires with Smaller Insulation	

FineAdjust Applicator 2037027100  
for L1NK300  
Receptacle Terminal,  
18-20 AWG Wires  
with Larger Insulation  
Extraction and 638132700  
Activation Tool

This document was generated on 08/24/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**