

TY400-50



CBL TIE 50LB 14IN NATURAL NYLON

General Information

Extended Product Type	TY400-50
Product ID	7TAG054360R0315
EAN	5414363064602
Catalog Description	CBL TIE 50LB 14IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 365.76mm (14.4 Inches), Width of 4.674mm (0.184 Inch), Thickness of 1.24mm (0.049 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Bulk Pack

Ordering

EAN	5414363064602
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.005 lb 2.268 g
--------------------	--------------------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	15 in 381 mm
Package Level 1 Height	4 in 102 mm
Package Level 1 Depth / Length	21 in 533 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	13.95 in 354 mm
Package Level 2 Height	13.5 in 343 mm
Package Level 2 Depth / Length	18.7 in 475 mm

Additional Information

Brand / Label	Ty-Fast
---------------	---------

Bundle Diameter	0.06 to 4.02 in 1.6 to 102 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Standard
Special Functions	The integrally formed nylon pawl combines low insertion and high locking strength.
Standards	UL E49405
Tensile Strength	50 lb 220 N
Thickness	0.049 in 1.24 mm
UPC	786210898544

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY400-50
Instructions and Manuals	TY400-50

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

