

GH195, FC310, GH663, 2781, SH222-16

Fittings
High Pressure

Hochdruck-
armaturen

Embouts
haute pression

Raccordi
alta pressione

Racores
altas pressione

51


DKOS Female
Swivel/O-Ring,
Heavy Duty

DKOS
Dichtkopf/O-Ring,
schwere Baureihe

DKOS avec joint
torique, série S

Femmina girevole
DKOS/O-Ring,
serie pesante

Hembra loca
DKOS con anillo
en O, serie pesada



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
11.721-10-4	M18x1,5		10	6	-4	66	35		4			22	22	
11.721-12-6	M20x1,5		12	10	-6	72	35		6			24	24	
11.721-14-6	M22x1,5		14	10	-6	72	35		8			27	27	
11.721-16-8	M24x1,5		16	12	-8	78	41		10			30	30	
11.721-20-10	M30x2,0		20	16	-10	82	44		13			36	36	
11.721-25-12	M36x2,0		25	19	-12	95	48		16			41	41	
11.721-30-16	M42x2,0		30	25	-16	106	55		21			50	50	
11.721-38-20	M52x2,0		38	31	-20	122	64		27			60	60	


DKOS Female
Swivel/O-Ring,
Heavy Duty, 45°
Elbow

DKOS
Dichtkopf/O-Ring,
schwere Baureihe,
45° Krümmer

DKOS avec joint
torique, série S
coudé 45°

Femmina girevole
DKOS/O-Ring a
45°, serie pesante

Hembra loca
DKOS acodado a
45° con anillo en
O, serie pesada



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
11.839-8-4	M16x1,5		8	6	-4	74	44	15	4			19	14	
11.839-10-4	M18x1,5		10	6	-4	77	46	17	4			22	14	
11.839-12-6	M20x1,5		12	10	-6	84	47	17	8			24	17	
11.839-16-8	M24x1,5		16	12	-8	107	69	25	10			30	22	
11.839-20-10	M30x2,0		20	16	-10	114	76	29	13			36	30	
11.839-25-12	M36x2,0		25	19	-12	141	94	36	16			41	32	
11.839-30-16	M42x2,0		30	25	-16	156	105	37	21			50	36	


DKOS Female
Swivel/O-Ring,
Heavy Duty, 90°
Elbow

DKOS
Dichtkopf/O-Ring,
schwere Baureihe,
90° Krümmer

DKOS avec joint
torique, serie S
coudé 90°

Femmina girevole
DKOS/O-Ring a
90°, serie pesante

Hembra loca
DKOS acodado a
90° con anillo en
O, serie pesada



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
11.840-10-4	M18x1,5		10	6	-4	68	38	35	4			22	14	
11.840-12-6	M20x1,5		12	10	-6	77	41	35	8			24	17	
11.840-16-8	M24x1,5		16	12	-8	96	58	51	10			30	22	
11.840-20-10	M30x2,0		20	16	-10	103	65	59	13			36	30	
11.840-25-12	M36x2,0		25	20	-12	128	82	75	16			41	32	
11.840-30-16	M42x2,0		30	19	-16	146	95	79	21			50	36	
11.840-38-20	M52x2,0		38	32	-20	158	100	82	27			60	46	