

FN1664-E

KIT 16GA FINISH NAILER-CT/ST 64MM MAX



Diameter: 1.6 - 1.6mm
Length: 25 - 64mm



Features



Rubber Comfort Grip



Magnesium Housing



No-Mar-Tip



Dial-A-Depth



Anti Slip Bumpers



Oil Free Engine



Rear Exhaust



Compact Nose



Rear Loading



Carry Case



Tool Lock-Out



Selectable Trigger



Locking Trigger



Belt Hook



SPECIFICATION

Power type	Pneumatic	Operating pressure	4.80 - 8.30 BAR
Weight	1.70 kg		70.00 - 120.00 PSI
Width	86 mm	Air Consumption Ltr.per shot @ 5.6 bar	1.83
Length	302 mm	Air fitting thread type	1/4 BSP
Height	289 mm	Noise	LPA 1sd 85.10
Magazine capacity (max)	110		LWA 1sd 89.20
SB16 Series Fasteners:			LPA 1s, 1m 76.20
Diameter (mm)	1.6 (min) 1.6 (max)	Vibration / Uncertainty	3.1 / 1.55 m/s ²
Length (mm)	25 (min) 64 (max)		
Head (mm)	3 (min) 3 (max)		
Collation angle	0		