



Product characteristics

Adapter plug

M12 connector

M20 - M12

Electrical data

Electrical design

DC

Operating voltage [V]

≤ 250

Current rating [A]

≤ 4

Environment

Ambient temperature [°C]

-25...85

Protection

IP 67

Mechanical data

Design

straight

Housing materials

polyamide

Mating cycles

> 500

Weight [kg]

0.012

Electrical connection

Connection

PVC cable / 0.07 m; 4 x 0.25 mm²

Wiring

1: brown

2: white

3: blue

4: black



1 BN

2 WH

3 BU

4 BK

Accessories

Accessories (included)

1 hexagon nut M20 x 1.5 / across flats 27

Remarks

Pack quantity

[piece]

1