

TECHNICAL SPECIFICATION

Product	DAR110	DAR120	DAR240	DAR260	DAR280
INPUTS	1	2	2	2	2
OUTPUTS	1	2	4	6	8
FREQUENCY RANGE	45-790MHz	45-230/470-790MHz	45-230/470-790MHz	45-230/470-790MHz	45-230/470-790MHz
GAIN	20dB+2	10dB+2	10dB+2	10dB+2	10dB+2
NOISE MAX	>3.5dB	>3.5dB	>3.5dB	>3.5dB	>3.5dB
MAX OUTPUT	102dB	78dB	78dB	78dB	78dB
ISOLATION BETWEEN PORTS	>20dB	>20dB	>20dB	>20dB	>20dB
RETURN PATH FREQUENCY	5-30MHz	5-30MHz	5-30MHz	5-30MHz	5-30MHz
IMPEDANCE	75ohm	75ohm	75ohm	75ohm	75ohm
CONNECTIONS	IEC	IEC	IEC	IEC	IEC
MAINS POWER	230V AC \pm 10% 50Hz Fitted Mains Plug BS1363 3A rating				