

## Hinges • adjustable

### 25161.0245



#### Product Description

Adjustable hinges can be positioned horizontally or vertically by moving the adjusting bushings in a form-fit and finely adjusted manner.

#### Material


##### Body

- Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

##### Axis

- Stainless Steel

#### Drawing



#### Order information

| Dimensions                                                       |                |                |                |                |                |                |                |                |                |   |   | Holding force  |                |                |  | Art. No.   |
|------------------------------------------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---|---|----------------|----------------|----------------|---------------------------------------------------------------------------------------|------------|
| b <sub>1</sub>                                                   | l <sub>1</sub> | b <sub>2</sub> | b <sub>3</sub> | d <sub>1</sub> | d <sub>2</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> | l <sub>2</sub> | s | x | F <sub>1</sub> | F <sub>2</sub> | F <sub>3</sub> | [g]                                                                                   |            |
| [mm]                                                             |                |                |                |                |                |                |                |                |                |   |   | [N]            |                |                |                                                                                       |            |
| adjustable in height and width – picture 1, Zinc die-cast, black |                |                |                |                |                |                |                |                |                |   |   |                |                |                |                                                                                       |            |
| 76                                                               | 60             | 42             | 33.5           | 6.5            | 8              | 15             | 9              | 8.5            | 34             | 4 | 1 | 1150           | 2000           | 2000           | 209                                                                                   | 25161.0245 |

## Compliance

### RoHS-compliant

Compliant with Directive 2011/65/EU [RoHS].

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 25.06.2025.

### SCIP-code

N/A

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

### POP-compliant

Contains no persistent organic pollutants – Stockholm Convention [POP] as of September 2025.

### PFAS-compliant

Contains no per- and polyfluoroalkyl substances (PFAS).

### TSCA-compliant

Agent concentration in this product does not exceed the specified threshold.