

## Coaxial Cable Connector 11\_SMA-50-4-50/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0039 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00167982
Catalogue drawing	DCA-00176269
Assembly instruction	DOC-0000347768

### Ordering Information

Bulk 500 pcs package	11_SMA-50-4-50/133_NP
Single package	11_SMA-50-4-50/133_NE

### Additional Information

Suitable cables	S_04172_D, S_04262_D, S_04272_B, LMR-240
-----------------	--