



datasheet for PKI 10 A  
 article number: 930103188



<b>product description:</b>	order number: 930 103-188
<b>description:</b>	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm.
<b>typ:</b>	PKI 10 A gelb/gruen yellow/green
<b>system:</b>	4 mm system
<b>order number:</b>	930 103-188
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>type of contact:</b>	spring unloaded socket
<b>type of termination:</b>	M 4 thread
<b>rated voltage:</b>	DC 60 V
<b>rated current:</b>	35 A
<b>contact resistance:</b>	2 mOhm
<b>mounting:</b>	screw
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	nickel-plated
<b>housing material:</b>	PF
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +100 °C
<b>inflammable class:</b>	
<b>housing:</b>	94 V-0
<b>drawing</b>	
	